


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-4 @20°C	0.055 ohms ±10%
D.C. RESISTANCE	5-6 @20°C	0.470 ohms ±10%
D.C. RESISTANCE	7-8 @20°C	0.108 ohms ±10%
INDUCTANCE	1-4 10kHz, 100mV, Ls	40.00uH ±10%
SATURATION CURRENT	1-4 20% rolloff from initial	1.75A
LEAKAGE INDUCTANCE	1-4 tie(5+6+7+8), 100kHz, 10mV, Ls	300nH typ., 600nH max.
DIELECTRIC	1-8 tie(6+7), 1875VAC, 1 second	1500VAC, 1 minute
DIELECTRIC	6-8 625VAC, 1 second	
URNS RATIO	(1-4):(8-7)	1:1
URNS RATIO	(6-5):(1-4)	1.5:1

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tape & Reel	Angles: ±1°	TRANSFORMER	750320550
		PKG-0328	Decimals: ±.005 [.13]		
		www.we-online.com/midcom	Fractions: ±1/64		
			Footprint: ±.005 [.13]		
6A	10/24	SEE REVISION SHEET FOR REVISION LEVEL	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750320550	SPECIFICATION SHEET 1 OF 1