


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID
 Ø.031(12)
 [.80]




TERM. NO.'s FOR REF. ONLY

.118 MIN.
 [3.00]




.583 MAX.
 [14.80]




LOT CODE & DATE CODE

1.260 MAX.
 [32.00]



RECOMMENDED
 P.C. PATTERN, COMPONENT SIDE



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-6 @20°C	0.285 ohms max.
INDUCTANCE	1-6 100kHz, 100mVAC, Ls	276.0uH ±10%
DIELECTRIC	1-10 600VAC, 1 second	-
TURNS RATIO	(1-6):(10-9)	9.857:1, ±2%
SELF-RESONANT FREQUENCY	1-6	1.700 MHz ref.

Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0841 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750340834
6A	11/11	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750340834	SPECIFICATION SHEET 1 OF 1