



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect


Midcom



Ø.0393(8)
[1.0]
PART MUST INSERT FULLY TO
SURFACE A IN RECOMMENDED GRID



CUSTOMER TIE TERMINAL
#1,2,3 AND 7,8,9 ON PCB.



RECOMMENDED
P.C. PATTERN, COMPONENT SIDE

ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-7 @20°C, tie(1+2+3, 7+8+9)	0.09 ohms max.
INDUCTANCE	1-7 @20°C, tie(1+2+3, 7+8+9)	220uH ±10%.
SATURATION CURRENT	1-7 20% rolloff from initial	15 A

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-TBD www.we-online.com/midcom	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13]	DRAWING TITLE INDUCTORE	PART NO. 750342313
00	03/14	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342313	SPECIFICATION SHEET 1 OF 1

