

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes


more than you expect




Midcom

ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:



PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	6-9 @20°C	0.200 ohms max.
D.C. RESISTANCE	8-7 @20°C	4.000 ohms max.
INDUCTANCE	6-9 50kHz, 100mVAC, Ls	230.0uH ±10%
DIELECTRIC	600VAC, 1 second	-
TURNS RATIO	(8-7):(6-9)	1.354:1, ±2%



TERM. NO.'s FOR REF. ONLY



LOT CODE & DATE CODE



RECOMMENDED P.C. PATTERN, COMPONENT SIDE

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0027 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750340990
6A	6/12	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750340990	compliant RoHS SPECIFICATION SHEET 1 OF 1