

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect





ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-1 @20°C	0.40 ohms max.
D.C. RESISTANCE	5-6 @20°C	0.53 ohms max.
D.C. RESISTANCE	10-8 @20°C	0.03 ohms max.
INDUCTANCE	3-1 50kHz, 100mVAC, Ls	800uH ±10%
LEAKAGE INDUCTANCE	3-1 tie(5+6+8+10), 100kHz, 100mVAC, Ls	10.0uH max.
DIELECTRIC	3-10 tie(3+5), 3000VAC, 1 second	-
DIELECTRIC	3-Core tie(3+5), 1500VAC, 1 second	-
URNS RATIO	(3-1):(10-8)	5.4:1, ±2%
URNS RATIO	(3-1):(5-6)	4.15:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified: Method: $\pm 1^\circ$ Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	Decimals: $\pm .005$ $[.13]$ Footprint: $\pm .001$ $[.03]$	DRAWING TITLE	PART NO.
		Method: Tray PKG-0967 www.we-online.com/midcom				TRANSFORMER	750342371
6A	10/17	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750342371	SPECIFICATION SHEET 1 OF 1

