



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.29 ohms max.
D.C. RESISTANCE	3-4 @20°C	0.14 ohms max.
D.C. RESISTANCE	5-8 @20°C	0.22 ohms max.
INDUCTANCE	1-2 100kHz, 1.0VAC, Ls	65uH ±15%
LEAKAGE INDUCTANCE	1-2 tie(3+4+5+8), 100kHz, 1.0VAC, Ls	1.5uH max.
DIELECTRIC	1-5 tie(2+3), 1250VDC, 1 second	1000VDC, 1 minute
TURNS RATIO	(1-2):(3-4)	2.75:1, ±2%
TURNS RATIO	(1-2):(5-8)	2.75:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: <b>Tape &amp; Reel</b> PKG-0193 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE <b>TRANSFORMER</b>	PART NO. <b>750341379</b>
6B	9/12	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341379	
6A	7/12					SPECIFICATION SHEET 1 OF 1