


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID
 #.024(4)
 [.60]





ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	9-13 @20°C	0.31 ohms max
D.C. RESISTANCE	1-2 @20°C	0.63 ohms max
INDUCTANCE	9-13 1kHz, 250mVAC, Ls	600uH ±10%
LEAKAGE INDUCTANCE	9-13 tie(1+2), 100kHz, 100mVAC, Ls	35.0 uH max
DIELECTRIC	1-9 1000VAC, 1 second	-
URNS RATIO	(9-13):(1-2)	4.923:1, ±2%

TERM. NO.'s FOR REF. ONLY

LOT CODE & DATE CODE



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

REFERENCE DESIGN

Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0239 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE INDUCTOR	PART NO. 750342425
00	5/14	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342425	compliant RoHS SPECIFICATION SHEET 1 OF 1