


| CUSTOMER TERMINAL | RoHS | LEAD(Pb)-FREE |
|-------------------|------|---------------|
| Sn96%, Ag4%       | Yes  | Yes           |

more than you expect




# ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

| PARAMETER       | TEST CONDITIONS                 | VALUE           |
|-----------------|---------------------------------|-----------------|
| D.C. RESISTANCE | 3-1 @20°C                       | 0.34 ohms max.  |
| D.C. RESISTANCE | 5-4 @20°C                       | 0.34 ohms max.  |
| D.C. RESISTANCE | 9-7 @20°C                       | 0.020 ohms max. |
| INDUCTANCE      | 3-1 10kHz, 100mVAC, Ls          | 450.0uH ±10%    |
| DIELECTRIC      | 1-9 tie(3+4), 3000VAC, 1 second | -               |
| URNS RATIO      | (3-1):(5-4)                     | 3:1, ±2%        |
| URNS RATIO      | (3-1):(9-7)                     | 7:1, ±2%        |



## ALTERNATE MARKING DETAIL



Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

| REV. | DATE  | Packaging Specifications<br>Method: Tray<br>PKG-0736<br>www.we-online.com/midcom | CONVENTION PLACEMENT | Tolerances unless otherwise specified:<br>Angles: ±1°<br>Fractions: ±1/64<br>Decimals: ±.005<br>Footprint: ±.001 | DRAWING TITLE<br><b>TRANSFORMER</b> | PART NO.<br><b>750341448</b> |
|------|-------|----------------------------------------------------------------------------------|----------------------|------------------------------------------------------------------------------------------------------------------|-------------------------------------|------------------------------|
| 6A   | 11/13 | SEE REVISION SHEET FOR REVISION LEVEL                                            |                      | This drawing is dual dimensioned. Dimensions in brackets are in millimeters.                                     | eiSos p/n: 750341448                | SPECIFICATION SHEET 1 OF 1   |

