





CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



TERM. NO.'s FOR REF. ONLY



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-1 @20°C	0.5 ohms max.
D.C. RESISTANCE	4-3 @20°C	0.91 ohms max.
D.C. RESISTANCE	5-6 @20°C	0.62 ohms max.
INDUCTANCE	5-6 100kHz, 1V, Ls	60uH ±10%
SATURATION CURRENT	20% rolloff from initial	1.0A
DIELECTRIC	4-5 tie(2+3), 1250VAC, 1 second	1000VAC, 1 minute
DIELECTRIC	1-Core tie(2+3), 1250VAC, 1 second	1000VAC, 1 minute
DIELECTRIC	5-Core 1250VAC, 1 second	1000VAC, 1 minute
URNS RATIO	(4-3):(2-1)	1.63:1, ±2%
URNS RATIO	(4-3):(5-6)	1.03:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0952 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750342460
6A	7/15	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342460	SPECIFICATION SHEET 1 OF 1