




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	1.214 ohms ±10%
D.C. RESISTANCE	2-3 @20°C	1.663 ohms ±10%
D.C. RESISTANCE	4-6 @20°C	0.446 ohms ±10%
D.C. RESISTANCE	S-F @20°C	0.075 ohms ±10%
INDUCTANCE	1-3 70kHz, 100mVAC, Ls	2.0mH ±10%
INDUCTANCE	S-F 70kHz, 100mVAC, Ls	42.0uH ±20%
LEAKAGE INDUCTANCE	1-3 tie(4+6+S+F), 70kHz, 100mVAC, Ls	20.0uH max.
DIELECTRIC	S-1 tie(3+4), 3750VAC, 1 second	-
URNS RATIO	(1-3):(4-6)	8.18:1, ±2%
URNS RATIO	(1-3):(S-F)	6.923:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Method: $\pm 1^\circ$ Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	Decimals: $\pm .005$ [.13] Footprint: $\pm .001$ [.03]	DRAWING TITLE	PART NO.
		Method: Tray PKG-0936 www.we-online.com/midcom				TRANSFORMER	750341585
6A	7/13	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750341585	SPECIFICATION SHEET 1 OF 1

