

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-5 @20°C	0.200 ohms max.
D.C. RESISTANCE	1-2 @20°C	0.150 ohms max.
D.C. RESISTANCE	6-9 tie(6+7, 8+9), @20°C	0.010 ohms max.
INDUCTANCE	4-5 10kHz, 100mVAC, Ls	360uH ±5%
LEAKAGE INDUCTANCE	4-5 tie(1+2, 6+7+8+9), 100kHz, 100mVAC, Ls	6.0uH max.
DIELECTRIC	4-6 tie(2+3, 6+7), 3000VAC, 1 second	-
URNS RATIO	(4-5):(1-2)	4.889:1, ±2%
URNS RATIO	(4-5):(6-9), tie(6+7, 8+9)	6.285:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:
- Reinforced insulation for a primary circuit at a working voltage of 265Vrms.



REV.	DATE	Packaging Specifications	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 Footprint: ±.001	DRAWING TITLE TRANSFORMER	PART NO. 750342655
6D	6/23	Method: Tray			
6C	7/18	PKG-0734			
6B	7/15	www.we-online.com/midcom			
6A	6/15	SEE REVISION SHEET FOR REVISION LEVEL	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342655	SPECIFICATION SHEET 1 OF 1