


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-1 @20°C	1.100 ohms max.
D.C. RESISTANCE	5-2 @20°C	0.757 ohms max.
D.C. RESISTANCE	3-4 @20°C	0.510 ohms max.
D.C. RESISTANCE	7-9 @20°C	0.165 ohms max.
INDUCTANCE	5-1 10kHz, 1.0VAC, L _s	0.8mH ±10%
LEAKAGE INDUCTANCE	5-1 tie(3+4, 7+9), 100kHz, 100mVAC, L _s	15.0uH max.
DIELECTRIC	1-9 tie(4+5), 3000VAC, 1 second	-
URNS RATIO	(5-1):(3-4)	2.66:1, ±2%
URNS RATIO	(5-1):(7-9)	3.47:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0887 www.we-online.com/midcom	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [1.3] Footprint: ±.001 [1.3]	DRAWING TITLE TRANSFORMER	PART NO. 750341696
6A	8/13	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341696	SPECIFICATION SHEET 1 OF 1

