

## ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER		TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2	@20°C	476uH±10%
D.C. RESISTANCE	7-6	@20°C	0.059 ohms max.
INDUCTANCE	1-2	50kHz, 100mVAC, Ls	0.148 ohms max.
DIELECTRIC	1-7	1250VAC, 1 second	1000VAC, 1 minute
TURNS RATIO		(1-2):(7-6)	1:1, ±2%

## **GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp. rise.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	
		Method: Tray	
		PKG-0101	
		www.we-online.com/midcom	
00	6/13	SEE REVISION SHEET FOR	

CONVENTION PLACEMENT
REVISION LEVEL

Tolerances unless otherwise specified:
Angles:  $\pm 1^{\circ}$  Decimals:  $\pm .005$  [.13]
Fractions:  $\pm 1/64$  Footprint:  $\pm .001$  [.03]

REMOVE TERMINAL#3, 4, 5, 8, 9 AND 10.

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

TRANSFORMER

eiSos p/n: 750341925

part no. 750341925

SPECIFICATION SHEET 1 OF 1