



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER		TEST CONDITIONS	VALUE
D.C. RESISTANCE	6-7	@20°C	0.227 ohms max.
D.C. RESISTANCE	10-9	@20°C	2.85 ohms max.
INDUCTANCE	6-7	50kHz, 100mV, Ls	0.25mH±10% max.
DIELECTRIC	6-10	1500VAC, 1 second	-
TURNS RATIO		(10-9):(6-7)	1.75:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.





Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

		I Devil and the Control of the Control
REV.	DATE	Packaging Specifications
		Method: Tray
		PKG-0027
		www.we-online.com/midcom
00	06/13	SEE REVISION SHEET FOR REVISION LEVEL

Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Footprint: ±.001 [.03] Fractions: ±1/64

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE INDUCTOR BUCK eiSos p/n: 750341951

PART NO.

750341951

