


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes


more than you expect



PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID  
.020 SQ.(4)  
[.51]



DOT LOCATES TERM. #1




TERM. NO.'s FOR REF. ONLY


LOT CODE & DATE CODE

**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	10-1 @20°C	0.51 ohms max.
D.C. RESISTANCE	10-6 @20°C	6.30 ohms max
INDUCTANCE	10-1 50kHz, 100mVAC, Ls	300 uH ±10%
URNS RATIO	(10-1):(10-6)	1.336:1, ±2%



85-265VAC  
40-50kHz



RECOMMENDED  
P.C. PATTERN, COMPONENT SIDE

**GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

REFERENCE DESIGN

Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0101 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE INDUCTOR	PART NO. 750342021
00	8/13	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342021	SPECIFICATION SHEET 1 OF 1