




more than you expect



[51]





ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to $+125^{\circ}\text{C}$ including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0816 www.we-online.com/midcom	 CONVENTIONAL PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750342805
6A	2/17	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTIONAL PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342805	 SPECIFICATION SHEET 1 OF 1