



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-4 tie(2+3, 4+5), @20°C	0.077 ohms max.
INDUCTANCE	2-4 tie(2+3, 4+5), 10kHz, 100mVAC, Ls	360.0uH ±10%
SATURATION CURRENT	20% rolloff from initial	9.2A

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Customer to tie terminals 2&3 and 4&5 on PCB.

Application of the transformer allows for the leadwires between terminals 2&3 and 4&5 to solder bridge.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$ Decimals: $\pm .005$ $[.13]$ Footprint: $\pm .001$ $[.03]$	DRAWING TITLE INDUCTOR	PART NO. 750342810
		Method: Tray PKG-1029 www.we-online.com/midcom				
6B	12/18	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342810	SPECIFICATION SHEET 1 OF 1
6A	8/15					

