


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes


more than you expect




PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID
 $\phi.031(9)$
 [.80]




TERM. NO.'s FOR REF. ONLY



LOT CODE & DATE CODE



Terminals #2 & 5 are tubed.



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-3 @20°C	0.220 ohms max.
D.C. RESISTANCE	5-2 @20°C	0.334 ohms max.
D.C. RESISTANCE	8-9 @20°C	0.210 ohms max.
D.C. RESISTANCE	10-9 @20°C	0.054 ohms max.
D.C. RESISTANCE	9-11 @20°C	0.054 ohms max.
INDUCTANCE	5-2 40kHz, 1VAC, Ls	1.50mH $\pm 8\%$
LEAKAGE INDUCTANCE	5-2 tie(3+4+8+9+10+11), 40kHz, 1VAC, Ls	47uH typ., 60uH max.
DIELECTRIC	5-8 tie(4+5), 4000VAC, 1 second	4000VAC, 1 minute
DIELECTRIC	5-Core tie(4+5), 2000VAC, 1 second	2000VAC, 1 minute
DIELECTRIC	8-Core 2000VAC, 1 second	2000VAC, 1 minute
URNS RATIO	(5-2):(4-3)	15:1, $\pm 2\%$
URNS RATIO	(5-2):(8-9)	15:1, $\pm 2\%$
URNS RATIO	(5-2):(10-9)	6.67:1, $\pm 2\%$
URNS RATIO	(5-2):(9-11)	6.67:1, $\pm 2\%$

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tray		Angles: $\pm 1^\circ$	TRANSFORMER	750342886
		PKG-1041		Fractions: $\pm 1/64$		
		www.we-online.com/midcom		Decimals: $\pm .005$ [.13]		
				Footprint: $\pm .001$ [.03]		
6A	12/16	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342886	SPECIFICATION SHEET 1 OF 1

