



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect





TERM. NO.'s FOR REF. ONLY



DOT LOCATES TERM. #1

LOT CODE & DATE CODE



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-4 @20°C	0.065 ohms max.
D.C. RESISTANCE	5-8 @20°C	0.020 ohms max.
INDUCTANCE	1-4 50kHz, 100mVAC, Ls	27.0uH ±10%
SATURATION CURRENT	1-4 20% rolloff from initial	1.8A
LEAKAGE INDUCTANCE	1-4 tie(5+8), 100kHz, 100mVAC, Ls	0.45uH max.
DIELECTRIC	1-5 1800VAC, 1 second	-
TURNS RATIO	(1-4):(5-8)	3:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0328 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750342975
6A	7/16	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342975	SPECIFICATION SHEET 1 OF 1