

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect




ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.964 ohms max.
D.C. RESISTANCE	4-3 @20°C	0.964 ohms max.
INDUCTANCE	1-2 10kHz, 50mVAC, Ls	34.00mH ±25%
INDUCTANCE	4-3 10kHz, 50mVAC, Ls	34.00mH ±25%
SATURATION CURRENT	tie(2+3), roll off 20% from initial	3A
LEAKAGE INDUCTANCE	tie(2+3), 10kHz, 50mVAC, Ls	500.0uH max.
DIELECTRIC	1-4 1875VAC, 1 second	1500VAC, 1 minute
DIELECTRIC	1-Core tie(1+4), 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(1-2):(4-3)	1:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to meet UL Recognized Insulation System M7-130(B), E106391.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 Footprint: ±.001	DRAWING TITLE	PART NO.
		Method: Tray PKG-0822 www.we-online.com/midcom			CMC	750342718
6A	8/15	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342718	SPECIFICATION SHEET 1 OF 1

