




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect




TERM. NO.'s FOR REF. ONLY



Application of the transformer allows for the leadwires between terminals 9&10 and 6&7 to solder bridge.

AREA REPRESENTS TERMINAL PAD DIMENSIONS



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.030 ohms max.
D.C. RESISTANCE	4-5 @20°C	0.120 ohms max.
D.C. RESISTANCE	9-7 @20°C	0.012 ohms max.
D.C. RESISTANCE	10-6 @20°C	0.012 ohms max.
INDUCTANCE	1-2 100kHz, 100mVAC, Ls	69uH min.
LEAKAGE INDUCTANCE	1-2 tie(4+5+6+7+9+10), 100kHz, 100mVAC, Ls	200nH max.
DIELECTRIC	1-9 tie(2+4, 9+10), 1500VAC, 1 second	-
TURNS RATIO	(1-2):(4-5)	1.25:1, ±2%
TURNS RATIO	(1-2):(9-6), tie(9+10, 7+6)	2.5:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0358 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750342756
6A	5/15	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342756	SPECIFICATION SHEET 1 OF 1