



CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-7 tie(4+5+6,7+8+9), @20°C	0.135 ohms max.
INDUCTANCE	4-7 tie(4+5+6,7+8+9),50kHz, 100mV, Ls	280.0µH ±10%
SATURATION CURRENT	4-7 tie(4+5+6,7+8+9), 20% rolloff from initial	18A



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Customer to tie terminals 4&5&6 and 7&8&9 internally on PC Board.

Application of transformer allows for leadwires between terminals 4&5&6 and 7&8&9 to solder bridge.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]	DRAWING TITLE	PART NO.
DATE	Method: Tray		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	INDUCTOR	750342940
ENG	YGD				
REV.	00				
DATE					
www.we-online.com/midcom		SPECIFICATION SHEET 1 OF 1			