



CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	5-6 @20°C	0.320 ohms max.
D.C. RESISTANCE	8-10 tie(8+9, 10+11), @20°C	0.042 ohms max.
INDUCTANCE	8-10 tie(8+9, 10+11),10kHz, 1V, Ls	120.0µH ±10%
DIELECTRIC	8-5 tie(8+9), 1875VAC, 1 second	
URNS RATIO	(8-10):(5-6), tie(8+9, 10+11)	7.5:1, ±2%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Application of solder bridge between terminal #8&9 and 10&11 is allowed.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM		Packaging Specifications	<p>Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03] This drawing is dual dimensioned. Dimensions in brackets are in millimeters.</p>	DRAWING TITLE	PART NO.
DATE		Method: Tray		INDUCTOR	750343038
ENG	NWA	PKG-0825			
REV.	00				
DATE	2015-9-24	www.we-online.com/midcom			
					SPECIFICATION SHEET 1 OF 1