





CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



TERM. NO.'s FOR REF. ONLY



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	0.021 ohms max.
D.C. RESISTANCE	9-10 @20°C	0.230 ohms max.
D.C. RESISTANCE	7-6 @20°C	0.230 ohms max.
INDUCTANCE	1-3 50kHz, 100mVAC, Ls	6.0uH ±10%
SATURATION CURRENT	1-3 20% rolloff from initial	6.5A
LEAKAGE INDUCTANCE	1-3 tie(7+6+9+10), 100kHz, 100mVAC, Ls	0.15uH max.
DIELECTRIC	1-10 tie(9+7), 1500VDC, 1 second	-
URNS RATIO	(10-9):(1-3)	2.4:1, ±2%
URNS RATIO	(10-9):(7-6)	1:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: <b>Tape &amp; Reel</b> PKG-0499 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE <b>TRANSFORMER</b>	PART NO. <b>750343077</b>
6A	1/17	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750343077	SPECIFICATION SHEET 1 OF 1