



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes




TERM. NO.'s FOR REF. ONLY




DOT LOCATES TERM. #1

LOT CODE & DATE CODE



Customer to tie terminals 6&7 and 9&10 internally on PCB.

Application of the transformer allows for the leadwires between terminals 6&7 and 9&10 to solder bridge.



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-5 @20°C	0.020 ohms max.
D.C. RESISTANCE	10-6 tie(6+7, 9+10), @20°C	0.007 ohms max.
D.C. RESISTANCE	2-1 @20°C	0.170 ohms max.
INDUCTANCE	3-5 50kHz, 100mVAC, Ls	9.0uH ±10%
LEAKAGE INDUCTANCE	3-5 tie(1+2+6+7+9+10), 100kHz, 100mVAC, Ls	165nH typ., 250nH max.
DIELECTRIC	5-6 tie(2+3, 6+7), 1875VAC, 1 second	-
6B TURNS RATIO	(3-5):(2-1)	1.8:1
6B TURNS RATIO	(3-5):(10-6), tie(6+7, 9+10)	3:1

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0499 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750342955
6B	9/22			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342955	SPECIFICATION SHEET 1 OF 1
6A	12/16	SEE REVISION SHEET FOR REVISION LEVEL				