


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-1 @20°C	1.120 ohms max.
D.C. RESISTANCE	5-4 @20°C	0.270 ohms max.
D.C. RESISTANCE	9-10 @20°C	0.080 ohms max.
INDUCTANCE	2-1 50kHz, 100mVAC, Ls	1300.0uH ±10%
LEAKAGE INDUCTANCE	2-1 tie(4+5+9+10), 100kHz, 100mVAC, Ls	15uH max.
DIELECTRIC	1-10 tie(3+4), 5000VDC, 1 second	5000VDC, 1 minute
DIELECTRIC	1-Core tie(3+4), 3125VDC, 1 second	2500VDC, 1 minute
DIELECTRIC	10-Core 3125VAC, 1 second	2500VDC, 1 minute
URNS RATIO	(2-1):(9-10)	6.67:1, ±2%
URNS RATIO	(2-1):(5-4)	5.33:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak, Overvoltage Category II.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tray		Angles: ±1°	TRANSFORMER	750342992
		PKG-0736		Decimals: ±.005 [1.3]		
6B	5/23	www.we-online.com/midcom		Fractions: ±1/64	Footprint: ±.001 [1.3]	
6A	10/16	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750342992	SPECIFICATION SHEET 1 OF 1