




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-4 @20°C	0.050 ohms max.
D.C. RESISTANCE	10-9 @20°C	0.087 ohms max.
D.C. RESISTANCE	7-6 @20°C	0.087 ohms max.
INDUCTANCE	2-4 50kHz, 100mVAC, Ls	33.00uH ±10%
SATURATION CURRENT	2-4 20% rolloff from initial	2.2A
LEAKAGE INDUCTANCE	2-4 tie(10+9+7+6), 100kHz, 100mVAC, Ls	0.30uH max.
DIELECTRIC	2-10 tie(9+7), 1875VAC, 1 second	-
URNS RATIO	(2-4):(9-10)	1:1, ±2%
URNS RATIO	(2-4):(6-7)	1:1, ±2%

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0499 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750343182
6A	4/20	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750343182	SPECIFICATION SHEET 1 OF 1