



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.250 ohms max.
D.C. RESISTANCE	4-6 @20°C	1.320 ohms max.
D.C. RESISTANCE	7-11 @20°C	0.040 ohms max.
D.C. RESISTANCE	12-9 @20°C	0.025 ohms max.
INDUCTANCE	4-6 50kHz, 100mVAC, Ls	998.0uH ±10%
LEAKAGE INDUCTANCE	4-6 tie(1+2+7+9+11+12), 100kHz, 100mVAC, Ls	9uH typ., 15uH max.
DIELECTRIC	6-7 tie(2+4, 11+12), 3750VAC, 1 second	-
DIELECTRIC	7-Core tie(11+12), 3750VAC, 1 second	-
URNS RATIO	(4-6):(1-2)	6.29:1, ±2%
URNS RATIO	(4-6):(7-11)	12.57:1, ±2%
URNS RATIO	(4-6):(12-9)	17.6:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Reinforced insulation for a primary circuit at a working voltage of 320Vrms, Overvoltage Category II.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [0.13] Footprint: ±.001 [0.03]	DRAWING TITLE	PART NO.
		Method: Tray PKG-0736 www.we-online.com/midcom			TRANSFORMER	750343074
6B	8/22	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750343074	SPECIFICATION SHEET 1 OF 1
6A	6/17					

