

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect





ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-5 tie(2+3, 5+6), @20°C	0.130 ohms max.
D.C. RESISTANCE	9-8 @20°C	0.033 ohms max.
INDUCTANCE	2-5 tie(2+3, 5+6), 10kHz, 100mVAC, Ls	600.0uH ±10%
SATURATION CURRENT	2-5 tie(2+3, 5+6), 20% rolloff from initial	3.7A
DIELECTRIC	2-8 4300VAC, 1 second	-
DIELECTRIC	2-Core 2150VAC, 1 second	-
DIELECTRIC	8-Core 2150VAC, 1 second	-
URNS RATIO	(2-5):(9-8), tie(2+3, 5+6)	10:1, ±2%


GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

CURRENT RATING: 4A



Application of the transformer allows for the leadwires between terminals 2&3 and 5&6 to solder bridge.



Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	Decimals: $\pm .005$ [.13] Footprint: $\pm .001$ [.03]	DRAWING TITLE	PART NO.
		Method: Tray PKG-0810 www.we-online.com/midcom				INDUCTOR	750343236
6A	5/19	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750343236	SPECIFICATION SHEET 1 OF 1

