




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.250 ohms max.
D.C. RESISTANCE	5-7 @20°C	0.320 ohms max.
INDUCTANCE	1-2 100kHz, 100mVAC, Ls	60.0uH ±10%
SATURATION CURRENT	1-2 20% rolloff from initial	1A
LEAKAGE INDUCTANCE	1-2 tie(5+7), 100kHz, 100mVAC, Ls	1.5uH max.
DIELECTRIC	2-5 2000VAC, 1 second	-
DIELECTRIC	2-Core 1000VAC, 1 second	-
DIELECTRIC	5-Core 1000VAC, 1 second	-
URNS RATIO	(5-7):(1-2)	1:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0121 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750343078
6A	1/17	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750343078	SPECIFICATION SHEET 1 OF 1