




more than you expect





PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	20.250 ohms max.
D.C. RESISTANCE	4-6 @20°C	0.365 ohms max.
INDUCTANCE	1-3 10kHz, 100mVAC, Ls	20.18mH ±12%
LEAKAGE INDUCTANCE	1-3 tie(4+6), 100kHz, 100mVAC, Ls	400uH max.
DIELECTRIC	1-4 1500VAC, 1 second	-
URNS RATIO	(1-3):(6-4)	12.61:1, ±1%

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0847 www.we-online.com/midcom	 CONVENTIONAL PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750343332
6A	9/17	SEE REVISION SHEET FOR REVISION LEVEL	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750343332 	SPECIFICATION SHEET 1 OF 1	