


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID




**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	11-1 tie(11+12, 1+2), @20°C	0.484 ohms max.
INDUCTANCE	11-1 tie(11+12, 1+2), 10kHz, 100mVAC, Ls	750.0uH ±10%
SATURATION CURRENT	11-1 tie(11+12, 1+2), 20% rolloff from initial	10A
DIELECTRIC	11-Core tie(11+12), 1250VAC, 1 second	-


**GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Customer to tie terminals 1+2 and 11+12 on PC board.

Application of the transformer allows for the leadwires between terminals 1&2 and 11&12 to solder bridge.



Wire insulation & RoHS status not affected by wire color.  
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-1029 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	Decimals: $\pm .005$ [.13] Footprint: $\pm .001$ [.03]	DRAWING TITLE <b>INDUCTOR</b>	PART NO. <b>750343229</b>
6B	6/20			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750343229	SPECIFICATION SHEET 1 OF 1
6A	10/17	SEE REVISION SHEET FOR REVISION LEVEL					