

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect





ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	5-3 @20°C	0.068 ohms max.
D.C. RESISTANCE	9-10 tie(8+9), @20°C	0.008 ohms max.
D.C. RESISTANCE	11-12 tie(12+13), @20°C	0.008 ohms max.
INDUCTANCE	5-3 100kHz, 100mVAC, Ls	560.00uH ±10%
LEAKAGE INDUCTANCE	5-3 tie(8+9+10+11+12+13), 100kHz, 100mVAC, Ls	72uH min., 80uH typ., 88uH max.
DIELECTRIC	5-8 tie(8+9+10+11), 4000VAC, 1 second	-
URNS RATIO	(5-3):(9-10), tie(8+9)	7:1, ±2%
URNS RATIO	(5-3):(11-12), tie(12+13)	7:1, ±2%


GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Customer to tie terminals 8+9 and 12+13 on PC board.

Application of the transformer allows for the leadwires between terminals 8&9 and 12&13 to solder bridge.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-1158 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750343230
6B	12/17			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750343230	SPECIFICATION SHEET 1 OF 1
6A	11/17	SEE REVISION SHEET FOR REVISION LEVEL				