

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:


PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-3	@20°C
D.C. RESISTANCE	S-F	@20°C
D.C. RESISTANCE	12-10	@20°C
INDUCTANCE	12-10	10kHz, 1V, L _s
LEAKAGE INDUCTANCE	12-10	tie(2+3+S+F), 100kHz, 100mVAC, L _s
DIELECTRIC	12-S	tie(2+12), 3750VAC, 1 second
DIELECTRIC	S-Core	3750VAC, 1 second
TURNS RATIO		(12-10):(S-F)
TURNS RATIO		(12-10):(3-2)

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak, Overvoltage Category II.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750343372
6C	6/19	Method: Tray PKG-1137 www.we-online.com/midcom				
6B	10/17					
6A	6/17	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750343372	SPECIFICATION SHEET 1 OF 1

