




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



Customer to tie terminals 2+3 on PC board.

Application of the transformer allows for the leadwires between terminals 2&3 to solder bridge.



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	6-7 @20°C	0.06 ohms max.
D.C. RESISTANCE	1-4 tie(2+3), @20°C	0.10 ohms max.
INDUCTANCE	6-7 800kHz, 100mVAC, Ls	22.00uH ±15%
LEAKAGE INDUCTANCE	6-7 tie(1+2+3+4), 100kHz, 100mVAC, Ls	200nH max.
DIELECTRIC	6-1 tie(2+3), 1500VAC, 1 second	-
URNS RATIO	(1-4):(6-7), tie(2+3)	1.5:1

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-1042 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750344204
6B	3/22			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750344204	
6A	7/21	SEE REVISION SHEET FOR REVISION LEVEL				SPECIFICATION SHEET 1 OF 1