

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes


more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-5 @20°C	0.625 ohms max.
D.C. RESISTANCE	1-2 @20°C	0.178 ohms max.
D.C. RESISTANCE	6-8 @20°C	0.075 ohms max.
D.C. RESISTANCE	9-10 @20°C	0.035 ohms max.
INDUCTANCE	4-5 100kHz, 100mVAC, Ls	350.00uH ±10%
LEAKAGE INDUCTANCE	4-5 tie(1+2+6+8+9+10), 100kHz, 100mV, Ls.	10.0uH max.
DIELECTRIC	5-6 tie(2+4, 8+9), 1875VAC, 1 second	-
DIELECTRIC	1-5 625VAC, 1 second	-
URNS RATIO	(5-4):(8-6)	4.8:1, ±2%
URNS RATIO	(5-4):(9-10)	14.4:1, ±2%
URNS RATIO	(5-4):(1-2)	4.8:1, ±2%

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tray		Angles: ±1°	TRANSFORMER	
		PKG-0887		Fractions: ±1/64		750343543
6B	12/20	www.we-online.com/midcom	CONVENTION PLACEMENT	Decimals: ±.005 [.13] Footprint: ±.001 [.03]		
6A	7/18	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750343543	SPECIFICATION SHEET 1 OF 1