





CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.16 ohms max.
D.C. RESISTANCE	7-10 @20°C	0.14 ohms max.
D.C. RESISTANCE	6-9 @20°C	0.18 ohms max.
D.C. RESISTANCE	4-5 @20°C	0.40 ohms max.
INDUCTANCE	1-2 250kHz, 100mV, Ls	600.00µH ±15%
LEAKAGE INDUCTANCE	1-2 tie(6+7+9+10),100kHz, 100mV, Ls	0.4µH typ., 0.8µH max.
DIELECTRIC	1-6 tie(2+4,7+9), 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(1-2):(7-10)	1:1, ±2%
URNS RATIO	(1-2):(6-9)	1:1, ±2%
URNS RATIO	(1-2):(4-5)	2:1, ±2%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications	<p>CONVENTION PLACEMENT</p>	<p>Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13]</p> <p>This drawing is dual dimensioned. Dimensions in brackets are in millimeters.</p>	<p>DRAWING TITLE</p> <p>TRANSFORMER</p>	<p>PART NO.</p> <p>750344343</p>
DATE	Method: Tape & Reel				
ENG	PKG-0499				
REV.	01				
DATE	2020/5/5	www.we-online.com/midcom			SPECIFICATION SHEET 1 OF 1