



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-6 @20°C	170 mOhms max.
D.C. RESISTANCE	1-2 @20°C	20 mOhms max.
D.C. RESISTANCE	8-11 @20°C	8 mOhms max.
D.C. RESISTANCE	11-10 @20°C	8 mOhms max.
INDUCTANCE	4-6 10kHz, 100mVAC, Ls	266.00uH ±10%
LEAKAGE INDUCTANCE	4-6 tie(1+2+8+10+11), 100kHz, 100mVAC, Ls	4uH max.
DIELECTRIC	6-8 tie(2+4), 5000VDC, 1 second	5000VDC, 1 minute
URNS RATIO	(4-6):(1-2)	4.89:1, ±2%
URNS RATIO	(4-6):(8-11)	11:1, ±2%
URNS RATIO	(4-6):(11-10)	14.67:1, ±2%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak, Overvoltage Category II.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0867 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750343773
6A	4/18	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750343773	SPECIFICATION SHEET 1 OF 1