


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-4 @20°C	1.94 ohms max.
D.C. RESISTANCE	4-5 @20°C	2.90 ohms max.
D.C. RESISTANCE	2-1 @20°C	0.056 ohms max.
D.C. RESISTANCE	9-8 @20°C	0.11 ohms max.
INDUCTANCE	3-5 10kHz, 100mVAC, Ls	1.60mH ±10%
LEAKAGE INDUCTANCE	3-5 tie(1+2+8+9), 100kHz, 100mVAC, Ls	29uH max.
DIELECTRIC	3-9 tie(2+5), 3750VAC, 1 second	-
TURNS RATIO	(3-4):(2-1)	4.27:1
TURNS RATIO	(3-4):(4-5)	1:1
TURNS RATIO	(3-4):(9-8)	4.27:1

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety standard undefined.

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0887 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE <b>TRANSFORMER</b>	PART NO. <b>750344399</b>
6A	8/22	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750344399	SPECIFICATION SHEET 1 OF 1