



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	1.73 ohms max.
D.C. RESISTANCE	5-6 @20°C	1.44 ohms max.
INDUCTANCE	5-6 10kHz, 100mVAC, Ls	400.00uH ±10%
LEAKAGE INDUCTANCE	5-6 tie(1+2), 100kHz, 100mVAC, Ls	15uH max.
DIELECTRIC	5-1 625VAC, 1 second	-
URNS RATIO	(5-6):(1-2)	1:1



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0410 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750344666
6A	4/21	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750344666	SPECIFICATION SHEET 1 OF 1