




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



\* DIMENSION MAY BE EXCEEDED WITH SOLDER ONLY



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER		TEST CONDITIONS	VALUE
D.C. RESISTANCE	S-F	@20°C	0.045 ohms max.
INDUCTANCE	S-F	10kHz, 100mVAC, Ls	200.00uH ±10%
SATURATION CURRENT	S-F	20% rolloff from initial	4.5A

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0239 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	Decimals: $\pm .005$ [.13] Footprint: $\pm .001$ [.03]	DRAWING TITLE <b>INDUCTOR</b>	PART NO. <b>750343802</b>
6B	3/20			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750343802	SPECIFICATION SHEET 1 OF 1
6A	9/18	SEE REVISION SHEET FOR	REVISION LEVEL				