




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.06 ohms max.
D.C. RESISTANCE	6-9 tie(6+7,9+10), @20°C	0.11 ohms max.
D.C. RESISTANCE	4-5 @20°C	0.14 ohms max.
INDUCTANCE	1-2 250kHz, 100mV, Ls	300.00µH ±15%
LEAKAGE INDUCTANCE	1-2 tie(6+7+9+10+4+5),250kHz, 100mV, Ls	0.5µH max.
DIELECTRIC	1-6 tie(2+4,6+7), 1875VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(6-9):(1-2), tie(6+7,9+10)	2:1, ±2%
URNS RATIO	(6-9):(4-5), tie(6+7,9+10)	4:1, ±2%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Customer to tie terminals 6+7 and 9+10 on PC board.
Application of the transformer allows for the leadwires between terminals 6&7 and 9&10 to solder bridge.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750344718
DATE	Method: Tape & Reel				
ENG	PKG-0358	www.we-online.com/midcom			
REV.	IYU				
DATE	2020/5/13				