




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



# **ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	S-F @20°C	0.035 ohms max.
INDUCTANCE	S-F 10kHz, 100mV, Ls	185.00µH ±12%
SATURATION CURRENT	S-F 30% rolloff from initial	26A Ref.




## **GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Rated current:16Arms

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM		Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
DATE		Method: Tray		Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13]		
ENG	SLC	PKG-0239		Fractions: $\pm 1/64$ Footprint: $\pm .005$ [.13]		
REV.	00					
DATE	2020/7/10	www.we-online.com/midcom		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	INDUCTOR	750344728