



CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-1 @20°C	0.504 ohms max.
D.C. RESISTANCE	5-6 @20°C	0.040 ohms max.
D.C. RESISTANCE	9-8 @20°C	0.005 ohms max.
D.C. RESISTANCE	12-11 @20°C	0.019 ohms max.
D.C. RESISTANCE	8-7 @20°C	0.027 ohms max.
INDUCTANCE	3-1 100kHz, 100mV, Ls	772µH ±10%
LEAKAGE INDUCTANCE	3-1 tie(5+6+7+8+9+11+12), 100kHz, 100mV, Ls	10µH max.
DIELECTRIC	1-12 tie(3+5,9+11), 3750VAC, 1 second	3000VAC, 1 minute
URNS RATIO	(3-1):(5-6)	15.25:1, ±2%
URNS RATIO	(3-1):(9-8)	15.25:1, ±2%
URNS RATIO	(3-1):(12-11)	10.17:1, ±2%
URNS RATIO	(3-1):(8-7)	15.25:1, ±2%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1,

EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak, Overvoltage Category II, Pollution Degree 2.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03] This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	DRAWING TITLE TRANSFORMER	PART NO. 750344264
DATE	Method: Tray				
ENG	HJH				
REV.	02				
DATE	2019/8/5	www.we-online.com/midcom			SPECIFICATION SHEET 1 OF 1