


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-1 @20°C	1.550 ohms max.
D.C. RESISTANCE	5-4 @20°C	0.115 ohms max.
D.C. RESISTANCE	9-8 @20°C	0.135 ohms max.
D.C. RESISTANCE	7-6 @20°C	0.035 ohms max.
INDUCTANCE	3-1 10kHz, 100mVAC, Ls	750.00uH ±10%
LEAKAGE INDUCTANCE	3-1 tie(6+7+8+9), 100kHz, 100mVAC, Ls	27uH max.
DIELECTRIC	2-9 tie(3+4, 7+8), 3750VAC, 1 second	3000VAC, 1 minute
DIELECTRIC	1-Core 500VAC, 1 second	-
URNS RATIO	(3-1):(5-4)	7:1
URNS RATIO	(3-1):(9-8)	7:1
URNS RATIO	(3-1):(7-6)	42:1

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to to meet creepage distance of 4mm min.

Designed to to meet clearance distance of 3mm min.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0887 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750344686
6A	3/24	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750344686	compliant RoHS SPECIFICATION SHEET 1 OF 1