

CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes



more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:


PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4,3-7,8 tie(3+4, 7+8), @20°C	0.007 ohms ±50%
INDUCTANCE	4,3-7,8 10kHz, 10mV, Ls	2.09µH ±5%
SATURATION CURRENT	4,3-7,8 20% rolloff from initial	8.5A

TERM. NO.'s FOR REF. ONLY



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Application of the transformer allows for the leadwires between terminals 3&4 and 7&8 to solder bridge.

Customer to tie terminals 3+4 and 7+8 on PC board.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

Preliminary

DFM	SP	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13]	DRAWING TITLE INDUCTOR	PART NO. 750371133
DATE	1/14/2020	Method: Tape & Reel PKG-0328		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
ENG	ANI					
REV.	00					
DATE	1/28/2020	www.we-online.com/midcom				SPECIFICATION SHEET 1 OF 1