


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	7-9 @20°C	5.30 ohms max.
D.C. RESISTANCE	11-12 @20°C	0.05 ohms max.
D.C. RESISTANCE	4-6 @20°C	0.08 ohms max.
INDUCTANCE	7-9 10kHz, 100mVAC, Ls	850.00uH ±10%
SATURATION CURRENT	7-9 20% rolloff from initial	0.7A
LEAKAGE INDUCTANCE	7-9 tie(4+6+11+12), 100kHz, 100mVAC, Ls	25uH max.
DIELECTRIC	7-6 tie(9+11), 3750VAC, 1 second	3000VAC, 1 minute
DIELECTRIC	7-12 500VAC, 1 second	-
URNS RATIO	(7-9):(12-11)	10.83:1
URNS RATIO	(7-9):(6-4)	13:1

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC62368-1, EN62368-1, UL62368-1/CSA62368-1 and AS/NZS62368.1:  
 - Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak, Overvoltage Category II, Pollution Degree 2.

Wire insulation & RoHS status not affected by wire color.  
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: <b>Tape &amp; Reel</b> PKG-0799 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE <b>TRANSFORMER</b>	PART NO. <b>750344830</b>
6A	4/23	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750344830	SPECIFICATION SHEET 1 OF 1