




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-6 @20°C	0.37 ohms max.
D.C. RESISTANCE	1-3 @20°C	0.30 ohms max.
INDUCTANCE	4-6 10kHz, 1V, Ls	150.00µH min.
LEAKAGE INDUCTANCE	4-6 tie(1+3),10kHz, 1V, Ls	5.5µH ±10%
DIELECTRIC	1-6 1500VAC, 1 second	
URNS RATIO	(4-6):(1-3)	1.22:1



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability. Marking method, font and color may vary on preproduction samples.

DFM	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13]	DRAWING TITLE	PART NO.
DATE	Method: Tape & Reel		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		
ENG	PKG-0637				
REV.	00				
DATE	2021/9/23	www.we-online.com/midcom			SPECIFICATION SHEET 1 OF 1