



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-3 @20°C	0.590 ohms max.
D.C. RESISTANCE	6-7 @20°C	0.830 ohms max.
INDUCTANCE	2-3 10kHz, 100mV, Cs	170.00uH min.
LEAKAGE INDUCTANCE	2-3 tie(6+7), 100kHz, 100mVAC, Cs	1uH max.
INTERWINDING CAPACITANCE	2-6 100kHz, 100mVAC, Cs	10pF max.
DIELECTRIC	3-6 5600VAC, 1 second	4480VAC, 1 minute
URNS RATIO	(7-6):(2-3)	1.4:1

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC62368-1, EN62368-1, UL62368-1/CSA62368-1 and AS/NZS62368.1:
- Basic insulation.

Designed to meet creepage distance at 6.2mm min. between primary and secondary.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750345408
6B	10/25	Method: Tray PKG-1336 www.we-online.com/midcom				
6A	11/24	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750345408	SPECIFICATION SHEET 1 OF 1

