




* DIMENSION MAY BE EXCEEDED WITH SOLDER ONLY









ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER		TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-4	@20°C	2.220 ohms ±10%
D.C. RESISTANCE	2-1	@20°C	0.529 ohms ±10%
D.C. RESISTANCE	5-8	@20°C	0.054 ohms ±20%
INDUCTANCE	3-4	10kHz, 100mVAC, Ls	1.5mH ±10%
INDUCTANCE	2-1	10kHz, 100mVAC, Ls	65.13uH ±10%
INDUCTANCE	5-8	10kHz, 100mVAC, Ls	8.44uH ±10%
SATURATION CURRENT	3-4	20% rolloff from initial	600mA
LEAKAGE INDUCTANCE	3-4	tie(2+1, 5+8), 100kHz, 100mVAC, Ls	32uH typ., 45uH max.
DISTRIBUTED CAPACITANCE	3-4	100mVAC, Cs	26.0pF typ.
DIELECTRIC	4-5	tie(2+3), 4875VAC, 1 second	3900VAC, 1 minute
DIELECTRIC	3-2	625VAC, 1 second	_
TURNS RATIO		(3-4):(5-8)	13.33:1, ±1%
TURNS RATIO		(3-4):(2-1)	4.8:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to $+125^{\circ}\text{C}$ including temp rise.

Designed to comply with the following requirements as defined by IEC61558-2-16 and EN61558-2-16:

 Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak (operating frequency of <2MHz).

Designed to comply with the following requirements as defined by IEC60950-1:

 Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak (operating frequency of <2MHz).

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

	5,112	Method: Tray PKG-0732
6B	1/23	www.we-online.com/midcom convention placement
6A	5/16	SEE REVISION SHEET FOR REVISION LEVEL

REV. DATE Packaging Specifications

Tolerances unless otherwise specified: Angles: $\pm 1^{\circ}$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE

TRANSFORMER

eiSos p/n: **750370423**

PART NO.

750370423

